### Xcelera-CL+ PX8 Full

PCI Express x8 Frame Grabber



#### **Key Features**

- · Half-length PCI Express x8 Board
- Acquires images from one Base,
   Medium or Full Camera Link<sup>®</sup> camera
- Rapid image acquisition and transfer rates beyond 1GB/s
- Supports Camera Link operations up to 85MHz
- Extended feature set supports advanced
   Camera Link pixel/tap configurations
- Windows\* XP and Windows 7 (32/64-bit) compatible
- · ROHS compliant
- On-board FPGA based real-time Bayer decoding and shading correction
- Power Over Camera Link (PoCL)
   Compliant
- Teledyne DALSA Platform Development Advantage – Free Run-time Licensing¹

## Advanced PCIe x8 image acquisition

Building on the field proven technology and performance of Teledyne DALSA's X64 frame grabbers the new X64 Xcelera Series leverages the PCI Express (PCIe) platform to bring traditional image acquisition and processing technology to new levels of performance and flexibility.

The PCIe host interface is a point-to-point host interface allowing simultaneous image acquisition and transfer without loading the system bus and involving little intervention from the host CPU. Designed with the requirements of the machine vision OEMs in mind, the Xcelera Series will range from entry level frame grabbers, to high-performance image acquisition boards, to embedded vision processors.

Addressing the emerging needs of bandwidth-hungry machine vision applications, Teledyne DALSA's Xcelera Series is defining next generation frame grabber capabilities with the ability to deliver bandwidth beyond 1GByte/s over multiple-lane PCI Express implementations with room to grow.

The X64 Xcelera-CL+ PX8 Full is a Camera Link frame grabber that is based on the PCI Express x8 interface. Compatible with a Base, Medium or Full Camera Link\* camera, the X64 Xcelera-CL+ PX8 Full supports a wide variety of multi-tap area and line scan colour and monochrome cameras. The X64 Xcelera-CL+ PX8 Full board can interface with advanced Camera Link camera output formats including 10-taps of 8-bit/pixel or 8-taps of 10-bit/pixel at 85MHz pixel clock rates.

The X64 Xcelera-CL+ PX8 Full has been built within Teledyne DALSA's Trigger-to-Image Reliability technology framework. Trigger-to-Image Reliability leverages Teledyne DALSA's hardware and software innovations to control, monitor and correct the image acquisition process from the time that an external trigger event occurs to the moment the data is sent to the host, providing traceability when errors do occur and permitting recovery from those errors.

#### **Software Support**

All of the frame grabbers in the Xcelera series are supported by Teledyne DALSA's Sapera Vision Software packages:

Sapera Essential, the core development platform, includes over 400 image processing primitive and industrial strength image analysis tools such as pattern finding, 1D and 2D barcode and OCR tools for part identification and detection, color processing tool, separation and measurement applications, blob analysis tool and inspection metrology tool for real-world dimensional measurements.

#### Teledyne DALSA Platform Development Advantage - Free Run-Time Licensing

The Sapera Essential standard processing tool run-time license is offered at no additional charge when combined with the Teledyne DALSA frame grabbers. This software run-time license' includes access to image processing functions, area-based (normalized correlation based) template matching tool, blob analysis and lens correction tool.

Sapera Nitrous accelerates Sapera Essential applications by providing a seamless support for graphical processing units (GPU) and multi-core CPUs optimization (MCO).

Sapera Architect Plus gives system integrators and industrial vision automation specialists a userfriendly, non-programming graphical environment to quickly prototype and test drive application specific imaging tools within Sapera Essential and Sapera Nitrous.





<sup>&</sup>lt;sup>1</sup>Some conditions and limitations apply, contact Teledyne DALSA sales for details.

# X64 Xcelera-CL+ PX8 Full PCI Express x8 Frame Grabber

| Function                           | Description  | Function  | Description  |
|------------------------------------|--|---|--|
|                                    |  |   |  |
| Board                              | Camera Link Specifications Rev 1.2 compatible Half length PCI Express 1.1 x8 compliant             | Controls  | Comprehensive event notification includes<br>start/end of frame/transfer events                    |
|                                    | ROHS Compliant   |   | Camera control signals for external event  |
| Acquisition                        | Supports one Base, Medium or Full Camera Link  |   | synchronization  |
|                                    | area and line scan camera  |   | Optically isolated trigger inputs programmable as active high or low                               |
| Resolution                         | Acquisition pixel clock rates from 20MHz to 85MHz Horizontal Size (min/max): 16 byte/256K bytes    |   | (edge or level trigger)  |
|                                    | Vertical Size (min/max):   |   | TTL Strobes outputs  |
|                                    | 1 line/infinite lines for line-scan cameras  |   | PC independent serial communications ports   |
|                                    | 1 line/16million lines/frame for area-scan cameras   |   | provide support 9600 to 11500K baud  Appear as system serial ports enabling seamless               |
|                                    | Variable length frame size from 1 to 16 million lines for area-scan cameras                        |   | interface to host applications   |
|                                    | 256MB onboard frame buffer memory  | Encoder Inputs  | Web synchronization using TTL/RS422 compatible   |
|                                    | Integrated advanced tap reversal engine allows   |   | quadrature (AB) encoder Optically isolated input up to 200KHz                                      |
|                                    | independent tap formatting   |   | RS422 input up to 5MHz   |
| Pixel Format and Tap configuration | Supports Camera Link tap configurations for 8, 10,   | On-board GPI/Os <sup>2</sup>  | 4-optically isolated general purpose inputs tolerate 5 and 24VDC signals 4 general purpose outputs |
|                                    | 12, 14 and 16-bit mono or 8, 10 or 12-bit RGB  |   |  |
|                                    | For Base cameras in any of the following   | Power Output  | PoCL Compliant (4W max)  |
|                                    | combinations:  | ations:<br>- tap, 2x10-bits/tap, 2x12-bit/tap,<br>/tap. 1x16-bits/tap. & 1x24-bit/RGB | Power-on-reset fused +12V output @ 1.5A  |
|                                    | 1x14-bit/tap, 1x16-bits/tap, & 1x24-bit/RGB  |   | +5V DC output at 1.5A  |
|                                    | For Medium camera - 4x8-bit/tap, 4x10-bits/tap,  | Software  | Device driver supports: Micrsoft Windows XP and Windows 7  |
|                                    | 4x12-bit/tap, 1x30-bit/RGB, & 1x36-bits/tap  |   | (32/64-bit) compatible   |
|                                    | For Full—8x 8-bit/tap Camera Link; 10-tap/8-bit and 8-tap/10-bit configurations                    |   | Full support of Teledyne DALSA DIGITAL   |
|                                    | Real-time transfers to system memory   |   | IMAGING's Sapera Essential, Sapera LT and Sapera Processing software libraries                     |
|                                    | Intelligent Data-Transfer-Engine automatically loads   |   | Application development using C++ and .Net   |
|                                    | scatter-gather and tap description tables from the   |   | languages(C++, C# or Visual Basic)   |
| On-board Processing                | host memory without CPU intervention   | System Requirements   | PCI Express Rev 1.1 compliant with one x8 slot   |
| Bayer Mosaic Filter                | Hardware Bayer Engine supports one Camera Link   | Discourage of the second  | system with 1024MB or higher system memory   |
| Bayer Mesale Filter                | Base 8, 10 or 12-bit Bayer   | Dimensions<br>Temperature   | 6.375" (16.1cm) Length X 4.20" (10.7 cm) Height 10°C (50° F) to 50° C (122° F)                     |
|                                    | Bayer output format supports 8, 10 or 12-bit RGB/  | remperature   | Relative Humidity: up to 90% (non-condensing)  |
|                                    | pixel  | Markings  | FCC Class B—Approved   |
| Shading Correction                 | Zero host CPU utilization for Bayer conversion On the fly Flat-line and Flat-field correction with | 5   | CE—Approved  |
|                                    | dead-pixel replacement   |   |  |
|                                    | Supports Camera Link Base, Medium or Full  |   |  |
|                                    | cameras  | 2 D in  | for the developt according   |
| Output Lookup Tables               | User programmable calibration gain/offset maps   | <sup>2</sup> Requires a separate slot   | for the bracket assembly   |
| Monochrome                         | Each input port has one 256x8-bit, 1024x10-bit,  |   |  |
| Worldownorm                        | 4096x12-bit OLUTs  |   |  |
| Colour                             | Each input port has one 8-bit in/out, 10-bit in 8 or   |   |  |
|                                    | 10-bit out, 12-bit in 12-bit/out Lookup table  |   |  |

#### www.teledynedalsa.com

Americas Europe Asia Pacific Boston, USA Munich, Germany Shanghai, China Tokyo, Japan +1 978-670-2000 +49 8142-46770 +81 3-5960-6353 +86 21-3368-0027 sales.americas@teledynedalsa.com sales.europe@teledynedalsa.com sales.asia@teledynedalsa.com sales.asia@teledynedalsa.com

